



## Pitcher, graduated, 1000 cc

|                              |                   |
|------------------------------|-------------------|
| <b>Proizvod #:</b>           | <b>2612853</b>    |
| EUR Cijena:                  | Kontaktirajte nas |
| Nije prikazan datum isporuke |                   |

Chemical-resistant, shatter-proof, tall-form pitchers with well-designed spouts, and large handles. Metric graduations are molded onto outside wall of each pitcher. Polypropylene, steam autoclavable at 250°F (121°C).

---

### Specifikacije

|                           |            |
|---------------------------|------------|
| Dubina:                   | 6.6 Inches |
| Graduations:              | 50 mL      |
| Kapacitet:                | 1000 mL    |
| Volumen/ veličina paketa: | 1 each     |